

XF705

4K Camcorder

Firmware ver. 1.0.1.1

Specifications

XF705

System

- **Recording System**

Clips:

XF-HEVC

Video compression: H.265 / HEVC

Audio format: Linear PCM, 24 bit, 48 kHz, 4 channels

File format: MXF

XF-AVC

Video compression: MPEG-4 AVC / H.264

Audio format: Linear PCM, 24 bit, 48 kHz, 4 channels

File format: MXF

Photos: DCF (Design rule for Camera File system), compatible with Exif Ver. 2.3, JPEG compression

- **Video Configuration¹ (recording/playback)**

XF-HEVC

Bit rate: 160 Mbps, 110 Mbps, 60 Mbps, 45 Mbps

Resolution: 3840x2160, 1920x1080

Color sampling: 4:2:2, 10 bit

Frame rate: 59.94i, 59.94P, 50.00i, 50.00P, 29.97P, 25.00P, 23.98P

XF-AVC

Bit rate: 45 Mbps

Resolution: 1920x1080

Color sampling: 4:2:0, 8 bit

Frame rate: 59.94P, 50.00P, 29.97P, 25.00P, 23.98P

¹ Available options may differ depending on the system frequency currently in use.

- **Recording Media (not included)**

For approximate recording times, refer to the *Reference Tables* (📖 224)

SD, SDHC (SD High Capacity) or SDXC (SD eXtended Capacity) card²; 2 slots for clips, only SD card B for photos

² SD card B is used also to save custom picture files, user memo files and the camcorder settings file.

- **Image Sensor**

Type 1.0 (1.0 in.) single-plate CMOS sensor

Effective pixels (approximate): 8,290,000 pixels (3840x2160)

- **LCD Touch Screen**

10.1 cm (4.0 in.) color LCD, 16:9 aspect ratio, approx.. 1,230,000 dots, 100% coverage, capacitive touch screen operation

- **Viewfinder:** 1.18 cm* (0.46 in.) organic LED display, approx. 1,770,000 dots*, 100% coverage

* When the language is set to simplified Chinese, the values with an asterisk are as follows:

1.09 cm (0.43 in.), approx. 1,555,000 dots.

- **Lens**

f=8.3 – 124.5 mm, F/2.8 – 4.5, 15x optical zoom, 9-bladed iris diaphragm

35mm equivalent focal length: approx. 28.3 – 424.6 mm (Dynamic IS)

approx. 25.5 – 382.5 mm (other IS modes)

- **Lens Configuration:** 18 elements in 14 groups (including 2 aspheric elements)

- **Filter Diameter:** 58 mm

- **Minimum Focusing Distance**

60 cm (2 ft.) throughout the zoom range; 1 cm (0.39 in.) at full wide angle

- **Shutter Speed**
Automatic, speed (normal or fine increments), angle, clear scan, slow shutter, off
- **Iris:** Manual, push auto iris, automatic aperture
- **Gain:** -6.0 dB to 33.0 dB, normal (3.0-dB) or fine (0.5-dB) increments
- **ND Filter:** Built-in (Off, 1/4, 1/16, 1/64), motor operated
- **Exposure:** AE shift, light metering modes (standard, spotlight, backlight)
- **White Balance**
Automatic white balance (AWB); custom white balance (two sets, A and B); two preset settings (daylight, 5,600 K³ and tungsten lamp, 3,200 K³); color temperature setting (2,000 K to 15,000 K)
Color temperature and color compensation (CC) adjustment available for all settings except custom white balance and AWB.
³ Color temperatures are approximate and given for reference purposes only.
- **Focus**
Manual focus, autofocus (Push AF, AF-boosted MF, continuous AF, Face AF); face detection and subject tracking available
AF type: Dual Pixel CMOS AF, contrast-detection AF
- **Image Stabilization**
Optical-shift image stabilizer + digital compensation (Standard IS, Dynamic IS, Powered IS)
- **Subject Illumination (gain 33.0 dB)**
59.94 Hz: 3 lux (59.94P, shutter speed 1/30)
50.00 Hz: 2.5 lux (50.00P, shutter speed 1/25)
- **Infrared mode:** Available, including built-in infrared light
- **Built-in microphone:** Stereo electret condenser microphone
- **Size of Photos:** 1920x1080

Wi-Fi

- **Wireless Standard:** IEEE802.11b/g/n (2.4 GHz band), IEEE802.11a/n (5 GHz band)
- **Connection Methods**
Infrastructure (Wi-Fi Protected Setup (WPS), search for access points, manual), Camera Access Point
- **Authentication Methods:** Open, shared key, WPA-PSK, WPA2-PSK
- **Encryption Methods:** WEP-64, WEP-128, TKIP, AES
- **Available Wi-Fi Channels**
Available Wi-Fi channels differ depending on the camcorder model. Check the identification label in the battery compartment (📖 17). Note also that not all Wi-Fi channels are available for Camera Access Point connections.
Model ID0117
2.4 GHz band: CH1 to CH11;
5 GHz band: CH56 to CH64 (Infrastructure only), CH149 to CH161 (Infrastructure/Camera Access Point)
Model ID0118
2.4 GHz band: CH1 to CH13;
5 GHz band: CH36 to CH64* (Infrastructure only)

* These channels are also prohibited for outdoor use in the following countries/regions:
Australia, Austria, Belgium, Bulgaria, Croatia, Cyprus, Czech Republic, Denmark, Estonia, Finland, France, Germany, Greece, Hong Kong S.A.R., Hungary, Iceland, Ireland, Italy, Latvia, Liechtenstein, Lithuania, Luxembourg, Malta, Netherlands, New Zealand, Norway, Poland, Portugal, Romania, Slovakia, Slovenia, Spain, Sweden, Switzerland, United Kingdom

Terminals

- **SDI Terminal**

BNC jack, output only, 0.8 Vp-p / 75 Ω, unbalanced

HD-SDI: SMPTE 292, SMPTE ST 299-1

3G-SDI: SMPTE 424, SMPTE 425, SMPTE ST 299-2

6G-SDI: SMPTE ST 2081

12G-SDI: SMPTE ST 2082

Embedded audio, time code (VITC/LTC)

Supplemental displays (superimposed onscreen displays, peaking, zebra pattern, magnification, waveform monitor) can also be output.

- **HDMI OUT Terminal**

HDMI connector, output only

Time code and supplemental displays (superimposed onscreen displays, peaking, zebra pattern, magnification, waveform monitor) can also be output.

- **INPUT Terminals (INPUT 1 and INPUT 2)**

XLR 3-pin jack (pin1: shield, pin2: hot, pin3: cold), 2 sets, balanced

Analog Inputs

MIC setting: -60 dBu (volume center, full scale -18 dB) / 600 Ω, microphone attenuator: 20 dB

LINE setting: 4 dBu (volume center, full scale -18 dB) / 10 kΩ

Digital Inputs (AES/EBU)

AES3 standard (48 kHz, 24 bit, 2ch) / 110 Ω

- **MIC Terminal**

∅ 3.5 mm stereo mini-jack, -72 dBV (manual volume center, full scale -18 dB) / 5.6 kΩ

Microphone attenuator: 20 dB

- **🎧 (headphone) Terminal**

∅ 3.5 mm stereo mini-jack, -∞ to -8 dBV (16 Ω load, volume range Min to Max) / 50 Ω or less

- **USB Terminal: mini-B receptacle, Hi-Speed USB, output only**

- **G-LOCK/SYNC Terminal**

BNC jack, 1.0 Vp-p / 75 Ω

GENLOCK setting: input only; SYNC OUT setting: output only, tri-level HD signal

- **TIME CODE Terminal**

BNC jack, input/output

Input setting: 0.5 Vp-p to 18 Vp-p / 100 kΩ; Output setting: 1.3 Vp-p / 50 Ω or less

- **REMOTE A Terminal, REMOTE B Terminal**

REMOTE A: ∅ 2.5 mm stereo sub-mini jack

REMOTE B: Circular 8-pin jack (for the optional RC-V100 Remote Controller, RS-422 interface)

- **🌐 (Ethernet) Terminal: Ethernet, 1000BASE-T compatible**

Power/Others

- **Power Supply (rated): 14.4 V DC (battery pack), 24.0 V DC (DC IN)**

- **Power Consumption (recording using the LCD screen with SDI terminal output enabled (3G-SDI))**

XF-HEVC clips, 3840x2160, 160 Mbps: 21.5 W (59.94P), 20.8 W (50.00P)

XF-HEVC clips, 1920x1080, 60 Mbps: 20.6 W (59.94P), 19.9 W (50.00P)

XF-AVC clips, 1920x1080, 45 Mbps: 19.1 W (59.94P), 18.8 W (50.00P)

- **Operating Temperature: 0 – 40 °C (32 – 104 °F)**

- **Dimensions (W x H x D)¹**
Camcorder body only: 162 x 210 x 378 mm (6.4 x 8.3 x 14.9 in.)
Camcorder body with lens hood, microphone holder and eye cup: 191 x 258 x 433 mm (7.5 x 10.2 x 17.0 in.)
¹ All dimensions are approximate.
- **Weight²**
Camcorder body (including the shoulder pad and grip belt): 2,710 g (6.0 lb.)
Typical working configuration*: 3,160 g (7.0 lb.)
* Camcorder with shoulder pad, grip belt, lens hood, microphone holder, eye cup, BP-A30 battery pack and one SD card.
² All weights are approximate.

CA-CP200 L Compact Power Adapter

- **Rated Input:** 100 – 240 V AC, 50/60 Hz, 90 VA – 120 VA
- **Rated Output:** 24 V DC, 1.8 A
- **Operating Temperature:** 0 – 40 °C (32 – 104 °F)
- **Dimensions (W x H x D):** 67.5 x 37 x 134 mm (2.7 x 1.5 x 5.3 in.)
- **Weight:** Approx. 290 g (10.2 oz.)

CG-A20 Battery Charger

- **Rated Input:** 24 V DC, 1.8 A
- **Rated Output:** 16.7 V DC, 1.5 A
- **Operating Temperature:** 0 – 40 °C (32 – 104 °F)
- **Dimensions (W x H x D):** 100 x 24 x 100 mm (3.9 x 0.9 x 3.9 in.)
- **Weight:** Approx. 145 g (5.1 oz.)

BP-A30 Battery Pack

- **Battery Type**
Rechargeable lithium ion battery, compatible with Intelligent System
- **Rated Voltage:** 14.4 V DC
- **Operating Temperature:** 0 – 40 °C (32 – 104 °F)
- **Rated Battery Capacity:** 3100 mAh / 45 Wh
- **Dimensions (W x H x D):** 41.5 x 45.1 x 69.7 mm (1.6 x 1.8 x 2.7 in.)
- **Weight:** Approx. 225 g (7.9 oz.)

Reference Tables

Approximate Recording Time on an SD Card

Approximate times, for reference only, based on a single recording that continues until the card is full.

Resolution and bit rate	SD card capacity			
	32 GB	64 GB	128 GB	256 GB
3840x2160, 160 Mbps	25 min.	50 min.	105 min.	210 min.
3840x2160, 110 Mbps	35 min.	75 min.	150 min.	305 min.
1920x1080, 60 Mbps	65 min.	140 min.	280 min.	565 min.
1920x1080, 45 Mbps	90 min.	185 min.	375 min.	755 min.

Charging Times

Charging times are approximate and vary according to charging conditions, ambient temperature and initial charge of the battery pack.

Battery pack	BP-A30 (supplied)	BP-A60 (optional)
Charging time using the supplied CG-A20 Battery Charger	170 min.	300 min.

Approximate Recording Times with a Fully Charged Battery Pack

The usage times in the following tables are approximate and were measured under the following conditions. Actual times may vary.

- “Typical recording” times measure recording times with repeated operations such as start/stop recording, zooming and turning on/off the camcorder.
- The effective usage time of the battery pack may decrease when using a bright screen setting, when recording in cold surroundings, etc.

Video configuration		Usage conditions	Battery pack	
Video format, resolution and bit rate	Frame rate		BP-A30 (supplied)	BP-A60 (optional)
XF-HEVC clips				
3840x2160, 160 Mbps	59.94P	Recording (maximum)	120 min.	245 min.
		Recording (typical)	65 min.	140 min.
		Playback	140 min.	280 min.
	50.00P	Recording (maximum)	125 min.	255 min.
		Recording (typical)	70 min.	145 min.
		Playback	140 min.	290 min.
1920x1080, 60 Mbps	59.94P	Recording (maximum)	125 min.	255 min.
		Recording (typical)	70 min.	145 min.
		Playback	145 min.	300 min.
	50.00P	Recording (maximum)	125 min.	260 min.
		Recording (typical)	70 min.	145 min.
		Playback	155 min.	315 min.

Video configuration		Usage conditions	Battery pack	
Video format, resolution and bit rate	Frame rate		BP-A30 (supplied)	BP-A60 (optional)
XF-AVC clips				
1920x1080, 45 Mbps	59.94P	Recording (maximum)	135 min.	280 min.
		Recording (typical)	80 min.	165 min.
		Playback	155 min.	325 min.
	50.00P	Recording (maximum)	135 min.	285 min.
		Recording (typical)	80 min.	165 min.
		Playback	160 min.	340 min.

㉞ (Ethernet) terminal159
 ㉟ (headphone) terminal103, 136

A

Abroad, using the camcorder217
 Access point153, 156
 Accessories218
 AE shift61
 AGC (automatic gain control)56
 AGC limit56
 Air vents49
 Aperture59
 Automatic aperture (auto iris)59
 Push auto iris60
 Assignable buttons117
 Audio output channels150
 Audio peak limiter101
 Audio recording95
 Audio recording level99
 Audio reference signal104
 AWB (auto white balance)66

B

Battery pack
 Battery information201, 219
 Charging19
 Remaining battery charge21, 201
 Bit rate51
 Browser Remote162
 Built-in backup battery216
 Button connection mode (WPS)156

C

Camcorder settings file129
 Camera Access Point155
 Canon Log 3 (gamma curve)63, 124
 Canon XF Utility (download)151
 Check marks (☑)107, 139

Clips

Adding an mark/ mark107, 139
 Adding/Deleting shot marks107, 141
 Clip information138
 Clip name format48
 Clip numbering48
 Copying139
 Deleting140
 Playback133
 Recording41
 Recovering37
 Saving to a computer151

Color bars104
 Color sampling51
 Color space63, 124
 Condensation217
 Connection to external devices145
 Conversion lens73
 Custom displays44
 Custom picture121
 Main settings124
 Other settings125
 Preset color settings63

D

Date and time23
 DC IN terminal21
 Digital tele-converter68
 Direct setting mode52
 Double slot recording36
 Drop frame (time code)89
 Dual Pixel Focus Guide75

E

Exposure compensation61

F

Face detection79
 Fan49
 FEC error correction174
 Flicker reduction55

Focus	74
AF-boosted MF	77
AF speed	78
Continuous AF	78
Face AF	79
Focus assistance functions	75
Focus limit	82
Manual focus	74
PUSH AF (momentary autofocus)	77
Tracking	81
Frame rate	50
Free-run (time code)	88
FTP transfer	176
Full auto mode	43

G

Gain	56
Gamma curve	63, 124
Genlock	92
G-LOCK/SYNC terminal	92, 94
GPS information	110, 203

H

HDMI OUT terminal	143, 146
HDR (high dynamic range)	124, 147
Headphones	103
HLG (hybrid log gamma curve)	124, 147
Hour meter	194, 201

I

Image stabilizer	83
Index screens	131
Infrared light	116
Infrared recording	116
Infrastructure	156
Initializing an SD card	35
INPUT 1/INPUT 2 terminals	95, 98
IP streaming	173
Iris	59

J

Joystick	25
Joystick guide	135

K

Key lock	43
----------	----

L

Language	24
LCD screen	30
Lens hood	28
Light metering mode	62
LUT (lookup table)	147

M

Macro shooting	82
Magnification	76
Menu settings	183
Message list	209
Metadata	108
MIC terminal	95, 97
Microphone	
Built-in	95
External	95, 97
Sensitivity / Attenuator / Low cut filter	101
Microphone holder unit	28, 97
My Menu	26

N

ND filter	58
Network connection	
Wi-Fi	154
Wired (Ethernet)	159
Network functions	153
Non-drop frame (time code)	89

O

OK marks (OK)	107, 139
Onscreen displays	44, 134
Onscreen markers	85

P

Peaking	76
Phantom power (microphone)	98
Photos	
Deleting	182
Recording	179
Viewing	181

PIN code connection mode (WPS)	157
Playback	
Clips	133
Photos	181
Power supply	19
POWER switch	22
Powered IS	83
Pre-recording	114

R

Rec run (time code)	88
Recording	
Clips	41
Photos	179
Reference tables (charging, usage and recording times, etc.)	224
Relay recording	36
REMOTE A, REMOTE B terminals	39
Remote controller	39
Remote operation	38, 39, 162
Resetting all camcorder settings	192
Resolution (frame size)	51
Reviewing a clip	112
Running mode (time code)	88

S

Safe area	85
SD card	
Compatible SD cards	33
Initializing	35
Inserting/Removing	34
Recording method	36
Switching SD card slots	35, 132
SDI terminal	145
Search for access points	157
Shooting frame rate	113
Shot marks	107, 141
Shoulder pad	32
Shoulder strap	31
Shutter speed	53
Slow motion recording	113
Special recording modes	113

Specifications	220
Status screens	195
Synchronization	92
System frequency	50

T

Tally lamps	42
Terminal covers	31
Time code	88
Time code synchronization	93, 94
TIME CODE terminal	93, 94
Tripod	32
Troubleshooting	204
Turning the camcorder on/off	22

U

USB terminal	110
User bit	91
User memo	108
User settings (user names/passwords for Browser Remote)	162

V

Video configuration	50
Video format (XF-HEVC, XF-AVC)	50
Video output configuration	143
Viewfinder	28, 30
Volume	136

W

Waveform monitor	105
White balance	65
Wide DR	63, 124
Wireless controller	38
WPS (Wi-Fi Protected Setup)	156

Z

Zebra pattern	86
Zoom	68
Customizable grip zoom speed patterns	70

CANON PROFESSIONAL DIGITAL VIDEO EQUIPMENT LIMITED WARRANTY FOR PRODUCTS PURCHASED IN THE UNITED STATES

The limited warranty set forth below is given by Canon U.S.A., Inc. ("Canon USA") with respect to Canon Professional Digital Video Equipment (the "Equipment") packaged with this limited warranty and purchased in the United States. This limited warranty is only effective upon presentation of your Bill of Sale or other proof of purchase. The Equipment is warranted to the original end-user purchaser, when delivered in new condition in its original container, under normal use against defective materials or workmanship as follows:

Parts: Defective parts will be exchanged for new parts or comparable rebuilt parts for a period of ONE YEAR from the date of original purchase.

Labor: For a period of ONE YEAR from the date of original purchase, labor will be provided free of charge by Canon USA's factory service centers or designated service facilities located in the United States.

When returning Equipment under this warranty, you must pre-pay the shipping charges, and you must enclose a copy of the Bill of Sale or other proof of purchase with a complete explanation of the problem. During the ONE-YEAR warranty period, repairs will be made and the Equipment will be returned to you free of charge. For repairs after the warranty period is over, you will be given an estimate of the cost of repair and an opportunity to approve or disapprove of the repair expense before it is incurred. If you approve, repairs will be made and the Equipment will be returned to you at your risk and expense. If you disapprove, we will return-ship the Equipment to you at no charge to you to an address within the United States.

This limited warranty only applies if the Equipment is used in conjunction with compatible computer equipment and compatible software, as to which items Canon USA will have no responsibility. Canon USA shall have no responsibility under this limited warranty for use of the Equipment in conjunction with incompatible peripheral equipment and/or incompatible software. Non-Canon brand peripheral equipment and software which may be distributed with, or factory loaded on, the Equipment, are sold 'AS IS' without warranty of any kind by Canon USA, including any implied warranty regarding merchantability or fitness for a particular purpose. The sole warranty with respect to such non-Canon brand items is given by the manufacturer or producer thereof. If the Equipment contains a hard disk drive, Canon USA recommends that data stored on that drive be duplicated or backed up to prevent its loss in the event of failure or other malfunction of such drive.

In order to obtain warranty service, please contact the authorized Canon retail dealer from whom you purchased the Equipment or contact the CANON INFORMATION CENTER AT 855-CINE-EOS (855-246-3367) or on the Internet at pro.usa.canon.com/support. You will be directed to the nearest service facility for your Equipment.

This Limited Warranty covers all defects encountered in normal use of the Equipment and does not apply in the following cases:

- A. Loss or damage to the Equipment due to abuse, mishandling, accident, improper maintenance, use of non-Canon accessories or failure to follow operating, maintenance or environmental instructions prescribed in Canon USA's user's manual;
- B. If the Equipment is defective as a result of leaking batteries, sand, dirt or water damage;
- C. If defects or damages are caused by the use of parts or supplies (other than those sold by Canon USA) that cause damage to the Equipment or that cause abnormally frequent service calls or service problems;
- D. If defects or damages are caused by service other than Canon USA's factory service centers or authorized service facilities;
- E. Any internal modification to product hardware or firmware;
- F. Any applicable fee for Maintenance of the Equipment;
- G. If the Equipment has had its serial number or dating altered or removed.

This Limited Warranty does not apply to Equipment purchased outside the United States. This Limited Warranty does not apply to accessories or consumables for the Equipment, which are sold "AS IS", without warranty of any kind by Canon USA. Please retain this warranty card and your Bill of Sale as a permanent record of your purchase. This card ensures that you are contacted promptly should there be a safety inspection, modification or product recall under applicable laws or regulations.

NO IMPLIED WARRANTY, INCLUDING MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE APPLIES TO THIS EQUIPMENT AFTER THE APPLICABLE PERIOD OF EXPRESS WARRANTY OR GUARANTY (EXCEPT AS MENTIONED ABOVE) GIVEN BY ANY PERSON, FIRM OR CORPORATION WITH RESPECT TO THIS EQUIPMENT SHALL BIND THE UNDERSIGNED (SOME STATES DO NOT ALLOW LIMITATIONS ON HOW LONG AN IMPLIED WARRANTY LASTS, SO THE ABOVE LIMITATION OR EXCLUSION MAY NOT APPLY TO YOU). CANON USA SHALL NOT BE LIABLE FOR LOSS OF REVENUES OR PROFITS, EXPENSE FOR SUBSTITUTE EQUIPMENT OR SERVICE, STORAGE CHARGES, LOSS OR CORRUPTION OF DATA, INCLUDING WITHOUT LIMITATION, LOSS OR CORRUPTION OF DATA STORED ON THE EQUIPMENT'S HARD DRIVE, OR ANY OTHER SPECIAL, INCIDENTAL OR CONSEQUENTIAL DAMAGES CAUSED BY THE USE, MISUSE OR INABILITY TO USE THE EQUIPMENT, REGARDLESS OF THE LEGAL THEORY ON WHICH THE CLAIM IS BASED, AND EVEN IF CANON USA HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES. NOR SHALL RECOVERY OF ANY KIND AGAINST CANON USA BE GREATER THAN THE PURCHASE PRICE OF THE EQUIPMENT SOLD BY CANON USA AND CAUSING THE ALLEGED DAMAGE. WITHOUT LIMITING THE FOREGOING, YOU ASSUME ALL RISK AND LIABILITY FOR LOSS, DAMAGE OR INJURY TO YOU AND YOUR PROPERTY AND TO OTHERS AND THEIR PROPERTY ARISING OUT OF USE, MISUSE OR INABILITY TO USE THE EQUIPMENT NOT CAUSED DIRECTLY BY THE NEGLIGENCE OF CANON USA (SOME STATES DO NOT ALLOW THE EXCLUSION OR LIMITATION OF INCIDENTAL OR CONSEQUENTIAL DAMAGES, SO THE ABOVE LIMITATION MAY NOT APPLY TO YOU). THIS WARRANTY SHALL NOT EXTEND TO ANYONE OTHER THAN THE ORIGINAL PURCHASER OF THIS EQUIPMENT OR THE PERSON FOR WHOM IT WAS PURCHASED AS A GIFT.

This warranty gives you specific legal rights, and you may also have other rights which vary from state to state.

CANON PROFESSIONAL DIGITAL VIDEO EQUIPMENT LIMITED WARRANTY FOR PRODUCTS PURCHASED IN CANADA

The limited warranty set forth below is given by Canon Canada Inc. ('Canon Canada') with respect to Canon Professional Digital Video Equipment (the 'Equipment') packaged with this limited warranty and purchased in Canada. This limited warranty is only effective upon presentation of your Bill of Sale or other proof of purchase. The Equipment is warranted to the original end-user purchaser, when delivered in new condition in its original container, under normal use against defective materials or workmanship as follows:

Parts: Defective parts will be exchanged for new parts or comparable rebuilt parts for a period of ONE YEAR from the date of original purchase.

Labor: For a period of ONE YEAR from the date of original purchase, labor will be provided free of charge by Canon Canada's factory service center or designated service facilities located in Canada.

When returning Equipment under this warranty, you must pre-pay the shipping charges, and you must enclose a copy of the Bill of Sale or other proof of purchase with a complete explanation of the problem. During the ONE-YEAR warranty period, repairs will be made and the Equipment will be return-shipped to you free of charge. For repairs after the warranty period is over, you will be given an estimate of the cost of repair and an opportunity to approve or disapprove of the repair expense before it is incurred. If you approve, repairs will be made and the Equipment will be returned to you at your risk and expense. If you disapprove, we will return-ship the Equipment to you at no charge to you to an address within Canada.

This limited warranty only applies if the Equipment is used in conjunction with compatible computer equipment and compatible software, as to which items Canon Canada will have no responsibility. Canon Canada shall have no responsibility under this limited warranty for use of the Equipment in conjunction with incompatible peripheral equipment and/or incompatible software. Non-Canon brand peripheral equipment and software which may be distributed with, or factory loaded on, the Equipment, are sold 'AS IS' without warranty of any kind by Canon Canada, including any implied warranty or condition regarding merchantability or fitness for a particular purpose. The sole warranty with respect to such non-Canon brand items is given by the manufacturer or producer thereof. If the Equipment contains a hard disk drive, Canon Canada recommends that data stored on that drive be duplicated or backed up to prevent its loss in the event of failure or other malfunction of such drive.

In order to obtain warranty service, please contact the authorized Canon retail dealer from whom you purchased the Equipment or contact the CANON PROFESSIONAL SERVICE CENTRE 1-800-667-2666 or on the Internet at www.canon.ca/pro. You will be directed to the nearest service facility for your Equipment.

This Limited Warranty covers all defects encountered in normal use of the Equipment and does not apply in the following cases:

- A. Loss or damage to the Equipment due to abuse, mishandling, accident, improper maintenance, use of non-Canon accessories or failure to follow operating, maintenance or environmental instructions prescribed in Canon Canada's user's manual;
- B. If the Equipment is defective as a result of leaking batteries, sand, dirt or water damage;
- C. If defects or damages are caused by the use of parts or supplies (other than those sold by Canon Canada) that cause damage to the Equipment or that cause abnormally frequent service calls or service problems;
- D. If defects or damages are caused by service other than Canon Canada's factory service centers or authorized service facilities;
- E. Any internal modification to product hardware or firmware;
- F. Any applicable fee for Maintenance of the Equipment;
- G. If the Equipment has had its serial number or dating altered or removed.

This Limited Warranty does not apply to Equipment purchased outside Canada. This Limited Warranty does not apply to accessories or consumables for the Equipment, which are sold "AS IS", without warranty of any kind by Canon Canada. Please retain this warranty card and your Bill of Sale as a permanent record of your purchase. This card ensures that you are contacted promptly should there be a safety inspection, modification or product recall under applicable laws or regulations.

NO IMPLIED WARRANTY OR CONDITION, INCLUDING MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE APPLIES TO THIS EQUIPMENT AFTER THE APPLICABLE PERIOD OF EXPRESS WARRANTY OR GUARANTY (EXCEPT AS MENTIONED ABOVE) GIVEN BY ANY PERSON, FIRM OR CORPORATION WITH RESPECT TO THIS EQUIPMENT SHALL BIND THE UNDERSIGNED (SOME PROVINCES DO NOT ALLOW LIMITATIONS ON HOW LONG AN IMPLIED WARRANTY OR CONDITION LASTS, SO THE ABOVE LIMITATION OR EXCLUSION MAY NOT APPLY TO YOU). CANON CANADA SHALL NOT BE LIABLE FOR LOSS OF REVENUES OR PROFITS, EXPENSE FOR SUBSTITUTE EQUIPMENT OR SERVICE, STORAGE CHARGES, LOSS OR CORRUPTION OF DATA, INCLUDING WITHOUT LIMITATION, LOSS OR CORRUPTION OF DATA STORED ON THE EQUIPMENT'S HARD DRIVE, OR ANY OTHER SPECIAL, INCIDENTAL OR CONSEQUENTIAL DAMAGES CAUSED BY THE USE, MISUSE OR INABILITY TO USE THE EQUIPMENT, REGARDLESS OF THE LEGAL THEORY ON WHICH THE CLAIM IS BASED, AND EVEN IF CANON CANADA HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES. NOR SHALL RECOVERY OF ANY KIND AGAINST CANON CANADA BE GREATER THAN THE PURCHASE PRICE OF THE EQUIPMENT SOLD BY CANON CANADA AND CAUSING THE ALLEGED DAMAGE. WITHOUT LIMITING THE FOREGOING, YOU ASSUME ALL RISK AND LIABILITY FOR LOSS, DAMAGE OR INJURY TO YOU AND YOUR PROPERTY AND TO OTHERS AND THEIR PROPERTY ARISING OUT OF USE, MISUSE OR INABILITY TO USE THE EQUIPMENT NOT CAUSED DIRECTLY BY THE NEGLIGENCE OF CANON CANADA (SOME PROVINCES DO NOT ALLOW THE EXCLUSION OR LIMITATION OF INCIDENTAL OR CONSEQUENTIAL DAMAGES, SO THE ABOVE LIMITATION MAY NOT APPLY TO YOU). THIS WARRANTY SHALL NOT EXTEND TO ANYONE OTHER THAN THE ORIGINAL PURCHASER OF THIS EQUIPMENT OR THE PERSON FOR WHOM IT WAS PURCHASED AS A GIFT.

This warranty gives you specific legal rights, and you may also have other rights which vary from province to province.